




Fig. 1




Fig. 2




Fig. 3

- Wrapost / Solder tail combinations are available in 3 lengths using MM pin numbers:
326...001 uses pin # 2601
326...002 uses pin # 2602
326...003 uses pin # 2603
See page 167 for details.
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1

Series 326...001

326-XX-1_-41-001000

Specify # of pins → 01-64

Fig. 2

Series 326...002

326-XX-1_-41-002000

Specify # of pins → 01-64

Fig. 3

Series 326...003

326-XX-1_-41-003000

Specify # of pins → 01-64

For Electrical,
Mechanical & Environmental
Data, See pg. 4

XX=Plating Code
See Below

For RoHS compliance
select ◇ plating code.

SPECIFY PLATING CODE XX=			93			43◇	
Sleeve (Pin)			5,08µm Sn/Pb			5,08µm Sn	
Contact (Clip)			0,76µm Au			0,76µm Au	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[326-93-164-41-003000](#) [326-93-164-41-002000](#) [326-93-132-41-003000](#) [326-93-132-41-002000](#) [326-93-120-41-003000](#) [326-93-120-41-002000](#) [326-43-164-41-003000](#) [326-43-164-41-002000](#) [326-43-132-41-003000](#) [326-43-132-41-002000](#) [326-43-120-41-003000](#)