

5275



Basic Part Number	# of Wraps	Wrapost Length A
5275-1	1	.370
5275-2	2	.470
5275-3	3	.610

5275-X-05-XX-00-00-01-0
Square press-fit in .035 plated thru hole


1010 ⇒ 1012/1020 ⇒ 1022



Basic Part Number	# of Wraps	Wrapost Length A	Head Dia. C
1012-1	1	.260	.072
1011-2	2	.360	
1010-3	3	.500	
1022-1	1	.260	.062
1021-2	2	.360	
1020-3	3	.500	

10XX-X-05-XX-00-00-01-0
Press-fit in .057 mounting hole

1215




1215-3-05-XX-00-00-01-0
Press-fit in .043 mounting hole

1124




1124-0-05-XX-00-00-01-0
Press-fit in .043 mounting hole

1210




1210-0-05-XX-00-00-01-0
Press-fit in .053 mounting hole

1222



1222-0-05-XX-00-00-01-0
Press-fit in .055 mounting hole

1221




1221-0-05-XX-00-00-01-0
Press-fit in .056 mounting hole

1110



1110-3-05-XX-00-00-01-0
Press-fit in .057 mounting hole

1094



1094-0-05-XX-00-00-01-0
Press-fit in .056 mounting hole

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 05 - XX - 00 - 00 - 01 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)
- ◇ 21 20μ" GOLD OVER NICKEL (RoHS)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1110-3-05-80-00-00-01-0](#) [1094-0-05-80-00-00-01-0](#) [1022-1-05-80-00-00-01-0](#) [1011-2-05-80-00-00-01-0](#) [1010-3-05-80-00-00-01-0](#) [1222-0-05-01-00-00-01-0](#) [1215-3-05-01-00-00-01-0](#) [1021-2-05-01-00-00-01-0](#) [1221-0-05-80-00-00-01-0](#)
[1011-2-05-15-00-00-01-0](#) [1011-2-05-21-00-00-01-0](#) [1094-0-05-21-00-00-01-0](#) [1110-3-05-15-00-00-01-0](#) [1110-3-05-21-00-00-01-0](#) [1124-0-05-15-00-00-01-0](#) [1222-0-05-15-00-00-01-0](#)