



0395



0395-X-15-XX-07-XX-10-0
Swage mount in .096 hole


Basic Part Number	Board Thickness	Length V
0395-1	.031	.062
0395-2	.062	.094
0395-3	.094	.125
0395-4	.125	.156
0395-5	.188	.219

8016




8016-0-15-XX-07-XX-10-0
Press-fit in .131 mounting hole

0350



0350-0-15-XX-07-XX-10-0
Hex press-fit in .129±.002 plated thru hole

8837



8837-0-15-XX-14-XX-10-0
Solder mount in .159 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 27 30μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#07 or #14 CONTACT (DATA ON PAGE 227)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0395-5-15-80-07-27-10-0](#) [0395-4-15-80-07-80-10-0](#) [0395-4-15-80-07-27-10-0](#) [0395-3-15-80-07-80-10-0](#) [0395-3-15-80-07-27-10-0](#) [0395-2-15-80-07-80-10-0](#) [0395-1-15-80-07-80-10-0](#) [0395-1-15-80-07-27-10-0](#) [0395-5-15-01-07-01-10-0](#) [0395-5-15-01-07-27-10-0](#) [0395-4-15-01-07-27-10-0](#) [0395-3-15-01-07-27-10-0](#) [0395-2-15-01-07-01-10-0](#) [0395-2-15-01-07-27-10-0](#) [0395-1-15-15-07-27-10-0](#) [0395-2-15-15-07-27-10-0](#) [0395-3-15-15-07-27-10-0](#) [0395-4-15-15-07-27-10-0](#)