



DUAL-IN-LINE HEADERS

SERIES 162, 862 • SHRINK DIP HEADER AND STRIPS, SOLDER TAIL



- High density DIP headers & strips for adapters and board stacking applications with 1,78 lead spacing
- Series 162 DIP headers and Series 862 strip headers use MM #6218 pins. See page 208 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION				
	A	B	C						
16	14,53	7,62	9,91	35	162-XX-316-00-180000				
28	25,20	10,16	12,45	20	162-XX-428-00-180000				
30	26,97	10,16	12,45	18	162-XX-430-00-180000				
48	42,98	10,16	12,45	12	162-XX-448-00-180000				
20	18,08	15,24	17,53	28	162-XX-620-00-180000				
28	25,20	15,24	17,53	20	162-XX-628-00-180000				
40	35,86	15,24	17,53	14	162-XX-640-00-180000				
42	37,64	15,24	17,53	13	162-XX-642-00-180000				
48	42,98	15,24	17,53	12	162-XX-648-00-180000				
52	46,53	15,24	17,53	11	162-XX-652-00-180000				
56	50,09	15,24	17,53	10	162-XX-656-00-180000				
64	57,20	15,24	17,53	9	162-XX-664-00-180000				
68	60,76	15,24	17,53	8	162-XX-668-00-180000				
64	57,20	19,05	21,34	8	162-XX-764-00-180000				
					SINGLE ROW STRIP HEADER If desired, we will supply any length up to 21 pins.				
21	37,64	---	2,64	---	862-XX-121-00-180000				
SPECIFY PLATING CODE XX =					10 ◆	90	40 ◆		
Pin Plating					0,25µm Au	5,08µm Sn/Pb	5,08µm Sn		

XX=Plating Code
See Below

RoHS-2
2011/65/EU



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[162-10-430-00-180000](#) [162-10-448-00-180000](#) [162-10-640-00-180000](#) [162-10-648-00-180000](#) [162-10-652-00-180000](#) [162-10-668-00-180000](#) [162-40-316-00-180000](#) [162-40-428-00-180000](#) [162-40-430-00-180000](#) [162-40-448-00-180000](#) [162-40-620-00-180000](#) [162-40-628-00-180000](#) [162-40-640-00-180000](#) [162-40-642-00-180000](#) [162-40-648-00-180000](#) [162-40-652-00-180000](#) [162-40-656-00-180000](#) [162-40-664-00-180000](#) [162-40-668-00-180000](#) [162-90-316-00-180000](#) [162-90-428-00-180000](#) [162-90-430-00-180000](#) [162-90-448-00-180000](#) [162-90-620-00-180000](#) [162-90-628-00-180000](#) [162-90-640-00-180000](#) [162-90-642-00-180000](#) [162-90-648-00-180000](#) [162-90-652-00-180000](#) [162-90-656-00-180000](#) [162-90-664-00-180000](#) [162-90-668-00-180000](#)