


MALE PCB PINS

SOLDER TERMINALS PIN TYPE

2318

2318-X-00-XX-00-00-07-0

Swage mount in 1,57 hole




Basic Part Number	Board Thickness	Length V
2318-1	0,79	1,30
2318-2	1,57	2,08
2318-3	2,39	2,87

2309

2309-X-00-XX-00-00-07-0

Swage mount in 1,63 hole




Basic Part Number	Board Thickness	Length V
2309-1	0,79	1,37
2309-2	1,57	2,13
2309-3	2,39	2,92
2309-4	3,18	3,73

2514

2514-2-00-XX-00-00-07-0

Press-fit in 1,78 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER
(60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2318-3-00-50-00-00-07-0](#) [2318-2-00-01-00-00-07-0](#) [2318-2-00-50-00-00-07-0](#) [2318-1-00-01-00-00-07-0](#) [2309-4-00-50-00-00-07-0](#) [2309-3-00-50-00-00-07-0](#) [2309-2-00-01-00-00-07-0](#) [2309-2-00-50-00-00-07-0](#) [2309-1-00-50-00-00-07-0](#) [2318-3-00-01-00-00-07-0](#) [2318-3-00-80-00-00-07-0](#) [2309-3-00-80-00-00-07-0](#) [2309-2-00-44-00-00-07-0](#) [2309-3-00-44-00-00-07-0](#) [2318-1-00-44-00-00-07-0](#) [2318-2-00-44-00-00-07-0](#) [2318-3-00-44-00-00-07-0](#)