


MALE PCB PINS

SOLDER TERMINAL TURRETS

2512

2512-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
2512-1	0,79	1,57
2512-2	1,57	2,39
2512-3	2,39	3,18
2512-4	3,18	3,96

2705

2705-X-00-XX-00-00-07-0

Swage mount in 3,28 hole




Basic Part Number	Board Thickness	Length V
2705-1	0,79	1,91
2705-2	1,57	2,67
2705-3	2,39	3,43
2705-4	3,18	4,19

2803

2803-X-00-XX-00-00-07-0

Swage mount in 2,87 hole




Basic Part Number	Board Thickness	Length V
2803-1	0,79	1,98
2803-2	1,57	2,77
2803-3	2,39	3,56
2803-4	3,18	4,34

2815

2815-X-00-XX-00-00-07-0

Swage mount in 2,87 hole




Basic Part Number	Board Thickness	Length V
2815-1	0,79	1,91
2815-2	1,57	2,67
2815-3	2,39	3,43
2815-4	3,18	4,19

2816

2816-X-00-XX-00-00-07-0

Swage mount in 2,95 hole




Basic Part Number	Board Thickness	Length V
2816-1	0,79	1,98
2816-2	1,57	2,77
2816-3	2,39	3,58
2816-4	3,18	4,37

2817

2817-X-00-XX-00-00-07-0

Swage mount in 2,95 hole



Basic Part Number	Board Thickness	Length V
2817-1	0,79	1,91
2817-2	1,57	2,67
2817-3	2,39	3,43
2817-4	3,18	4,19

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER
(60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2817-4-00-01-00-00-07-0](#) [2817-4-00-50-00-00-07-0](#) [2817-3-00-01-00-00-07-0](#) [2817-3-00-50-00-00-07-0](#) [2817-2-00-01-00-00-07-0](#) [2817-2-00-50-00-00-07-0](#) [2817-1-00-01-00-00-07-0](#) [2817-1-00-50-00-00-07-0](#) [2816-4-00-01-00-00-07-0](#) [2816-4-00-50-00-00-07-0](#) [2816-3-00-50-00-00-07-0](#) [2816-2-00-50-00-00-07-0](#) [2816-1-00-01-00-00-07-0](#) [2816-1-00-50-00-00-07-0](#) [2815-4-00-01-00-00-07-0](#) [2815-4-00-50-00-00-07-0](#) [2815-3-00-50-00-00-07-0](#) [2815-2-00-50-00-00-07-0](#) [2815-1-00-01-00-00-07-0](#) [2815-1-00-50-00-00-07-0](#) [2803-4-00-01-00-00-07-0](#) [2803-4-00-50-00-00-07-0](#) [2803-3-00-01-00-00-07-0](#) [2803-3-00-50-00-00-07-0](#) [2803-2-00-01-00-00-07-0](#) [2803-2-00-50-00-00-07-0](#) [2803-1-00-50-00-00-07-0](#) [2705-4-00-01-00-00-07-0](#) [2705-4-00-50-00-00-07-0](#) [2705-3-00-01-00-00-07-0](#) [2705-3-00-50-00-00-07-0](#) [2705-2-00-50-00-00-07-0](#) [2705-1-00-50-00-00-07-0](#) [2512-4-00-01-00-00-07-0](#) [2512-4-00-50-00-00-07-0](#) [2512-3-00-50-00-00-07-0](#) [2512-2-00-01-00-00-07-0](#) [2512-2-00-50-00-00-07-0](#) [2512-1-00-50-00-00-07-0](#) [2817-4-00-80-00-00-07-0](#) [2817-3-00-80-00-00-07-0](#) [2817-2-00-80-00-00-07-0](#) [2817-1-00-80-00-00-07-0](#) [2816-4-00-80-00-00-07-0](#) [2816-3-00-80-00-00-07-0](#) [2816-2-00-80-00-00-07-0](#) [2816-1-00-80-00-00-07-0](#) [2815-4-00-80-00-00-07-0](#) [2815-3-00-80-00-00-07-0](#) [2815-2-00-80-00-00-07-0](#) [2815-1-00-80-00-00-07-0](#) [2803-4-00-80-00-00-07-0](#) [2803-3-00-80-00-00-07-0](#) [2803-1-00-80-00-00-07-0](#) [2705-4-00-80-00-00-07-0](#) [2705-3-00-80-00-00-07-0](#) [2705-2-00-80-00-00-07-0](#) [2705-1-00-80-00-00-07-0](#) [2512-4-00-80-00-00-07-0](#) [2512-2-00-80-00-00-07-0](#) [2512-2-00-44-00-00-07-0](#) [2512-3-00-44-00-00-07-0](#) [2512-4-00-44-00-00-07-0](#) [2705-1-00-44-00-00-07-0](#) [2705-2-00-44-00-00-07-0](#) [2705-3-00-44-00-00-07-0](#) [2705-4-00-44-00-00-07-0](#) [2803-2-00-44-00-00-07-0](#) [2803-3-00-44-00-00-07-0](#) [2803-4-00-44-00-00-07-0](#) [2815-1-00-44-00-00-07-0](#) [2815-2-00-44-00-00-07-0](#) [2815-3-00-44-00-00-07-0](#) [2815-4-00-44-00-00-07-0](#) [2816-1-00-44-00-00-07-0](#) [2816-2-00-44-00-00-07-0](#) [2816-3-00-44-00-00-07-0](#) [2816-4-00-44-00-00-07-0](#) [2817-1-00-44-00-00-07-0](#) [2817-2-00-44-00-00-07-0](#) [2817-3-00-44-00-00-07-0](#) [2817-4-00-44-00-00-07-0](#)