



DUAL-IN-LINE SOCKETS

SERIES 114 • SURFACE MOUNT, STUB TAIL • OPEN FRAME



- Unique floating contacts compensate for the effects of unevenly dispensed solder paste
- Socket pins feature closed end construction eliminating any solder/flux wicking problems
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 114 uses MM #1434 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION		
	A	B	C				
10	12,6	5,08	7,6	41	114-XX-210-41-117000		
4	5,0	7,62	10,1	100	114-XX-304-41-117000		
6	7,6	7,62	10,1	67	114-XX-306-41-117000		
8	10,1	7,62	10,1	50	114-XX-308-41-117000		
10	12,6	7,62	10,1	40	114-XX-310-41-117000		
14	17,7	7,62	10,1	28	114-XX-314-41-117000		
16	20,3	7,62	10,1	25	114-XX-316-41-117000		
18	22,8	7,62	10,1	22	114-XX-318-41-117000		
20	25,3	7,62	10,1	20	114-XX-320-41-117000		
22	27,8	7,62	10,1	18	114-XX-322-41-117000		
24	30,4	7,62	10,1	16	114-XX-324-41-117000		
28	35,5	7,62	10,1	14	114-XX-328-41-117000		
20	25,4	10,16	12,7	20	114-XX-420-41-117000		
22	27,8	10,16	12,7	18	114-XX-422-41-117000		
24	30,4	10,16	12,7	16	114-XX-424-41-117000		
28	35,5	10,16	12,7	14	114-XX-428-41-117000		
32	40,6	10,16	12,7	12	114-XX-432-41-117000		
24	30,4	15,24	17,7	16	114-XX-624-41-117000		
28	35,5	15,24	17,7	14	114-XX-628-41-117000		
32	40,6	15,24	17,7	12	114-XX-632-41-117000		
36	45,7	15,24	17,7	11	114-XX-636-41-117000		
40	50,8	15,24	17,7	10	114-XX-640-41-117000		
42	53,3	15,24	17,7	9	114-XX-642-41-117000		
48	60,9	15,24	17,7	8	114-XX-648-41-117000		
50	63,5	15,24	17,7	8	114-XX-650-41-117000		
52	66,0	15,24	17,7	7	114-XX-652-41-117000		
50	63,5	22,86	25,3	8	114-XX-950-41-117000		
52	66,0	22,86	25,3	7	114-XX-952-41-117000		
64	81,2	22,86	25,3	6	114-XX-964-41-117000		
SPECIFY PLATING CODE XX =							
Sleeve (Pin)					91	93	41 ◆
Contact (Clip)					5,08μm Sn/Pb	5,08μm Sn/Pb	43 ◆
					0,25μm Au	0,76μm Au	47 ◆

XX=Plating Code
See Below

RoHS-2
2011/65/EU



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[114-41-952-41-117000](#) [114-91-316-41-117000](#) [114-91-424-41-117000](#) [114-91-642-41-117000](#) [114-41-428-41-117000](#) [114-41-640-41-117000](#) [114-41-642-41-117000](#) [114-91-210-41-117000](#) [114-91-318-41-117000](#) [114-91-320-41-117000](#) [114-91-652-41-117000](#) [114-41-628-41-117000](#) [114-41-950-41-117000](#) [114-91-308-41-117000](#) [114-91-636-41-117000](#) [114-91-964-41-117000](#) [114-41-306-41-117000](#) [114-41-324-41-117000](#) [114-41-328-41-117000](#) [114-41-310-41-117000](#) [114-41-320-41-117000](#) [114-41-322-41-117000](#) [114-41-624-41-117000](#) [114-91-310-41-117000](#) [114-91-422-41-117000](#) [114-91-640-41-117000](#) [114-41-304-41-117000](#) [114-41-652-41-117000](#) [114-91-420-41-117000](#) [114-41-422-41-117000](#) [114-91-432-41-117000](#) [114-41-314-41-117000](#) [114-41-420-41-117000](#) [114-91-322-41-117000](#) [114-91-624-41-117000](#) [114-91-650-41-117000](#) [114-41-636-41-117000](#) [114-91-314-41-117000](#) [114-91-428-41-117000](#) [114-41-308-41-117000](#) [114-41-632-41-117000](#) [114-41-964-41-117000](#) [114-91-648-41-117000](#) [114-41-316-41-117000](#) [114-41-318-41-117000](#) [114-41-648-41-117000](#) [114-91-304-41-117000](#) [114-91-324-41-117000](#) [114-91-632-41-117000](#) [114-91-950-41-117000](#) [114-91-952-41-117000](#) [114-41-424-41-117000](#) [114-41-432-41-117000](#) [114-41-650-41-117000](#) [114-91-306-41-117000](#) [114-91-328-41-117000](#) [114-91-628-41-117000](#) [114-47-308-41-117000](#) [114-47-648-41-117000](#) [114-47-640-41-117000](#) [114-47-642-41-117000](#) [114-47-636-41-117000](#) [114-47-950-41-117000](#) [114-47-964-41-117000](#) [114-47-328-41-117000](#) [114-47-428-41-117000](#) [114-47-316-41-117000](#) [114-47-322-41-117000](#) [114-47-420-41-117000](#) [114-47-320-41-117000](#) [114-47-422-41-117000](#) [114-47-314-41-117000](#) [114-47-632-41-117000](#) [114-47-210-41-117000](#) [114-47-424-41-117000](#) [114-47-306-41-117000](#) [114-47-952-41-117000](#) [114-47-318-41-117000](#) [114-47-628-41-117000](#) [114-47-310-41-117000](#) [114-47-652-41-117000](#) [114-47-432-41-117000](#) [114-47-650-41-117000](#) [114-47-324-41-117000](#) [114-47-304-41-117000](#)