



1052/1053



Basic Part Number	# of Wraps	Length A
1053-2	2	.360
1052-3	3	.515

105X-X-17-XX-34-XX-02-0
Press-fit in .083 mounting hole


0383



Basic Part Number	Board Thickness	Length V
0383-1	.062	.094
0383-2	.094	.125
0383-3	.125	.156

0383-X-17-XX-34-XX-02-0
Swage mount in .094 hole

0382



0382-3-17-XX-34-XX-02-0
Press-fit in .089 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 17 - XX - 34 - XX - 02 - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
15 10 μ " GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
14 10 μ " GOLD OVER NICKEL
27 30 μ " GOLD OVER NICKEL

SELECT CONTACT

#34 CONTACT (DATA ON PAGE 212)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0383-2-17-15-34-14-02-0](#) [0382-3-17-15-34-14-02-0](#) [0383-1-17-15-34-14-02-0](#) [0383-3-17-15-34-14-02-0](#)