

0512	2218	0703	0574
0512-0-15-XX-12-XX-04-0 Press-fit in .057 mounting hole	2218-0-15-XX-22-XX-10-0 Press-fit in .057 mounting hole	0703-0-15-XX-12-XX-04-0 Press-fit in .057 mounting hole	0574-0-15-XX-12-XX-04-0 Press-fit in .057 mounting hole
0468	0550	0671	0707
0468-0-15-XX-12-XX-04-0 Press-fit in .057 mounting hole	0550-0-15-XX-22-XX-10-0 Solder mount in .052 min. mounting hole	0671-0-15-XX-12-XX-10-0 Solder mount in .063 min. mounting hole	0707-0-15-XX-12-XX-10-0 Solder mount in .051 min. mounting hole
5739	8894		
5739-0-18-XX-12-XX-10-0 Surface mount Also available on 16mm wide carrier tape: 3,000 parts per 13" reel. Order as: 5739-0-67-XX-12-XX-10-0	8894-0-15-XX-12-XX-10-0 Hex press-fit in .059 plated thru hole		
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0 BASIC PART # SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: 02 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL SELECT CONTACT #12 or #22 CONTACT (DATA ON PAGE 207)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0574-0-15-15-12-14-04-0](#) [0512-0-15-15-12-14-04-0](#)