



0444



Basic Part Number	# of Wraps	Length A
0444-1	1	.260
0444-2	2	.370
0444-3	3	.505

0444-X-17-XX-30-XX-02-0
Press-fit in .056 mounting hole


0445/0446



Basic Part Number	# of Wraps	Length A
0446-2	2	.370
0445-3	3	.505

044X-X-17-XX-30-XX-02-0
Press-fit in .056 mounting hole


2601⇒2603



Basic Part Number	# of Wraps	Length A
2601-0	1	.232
2602-0	2	.350
2603-0	3	.468

260X-X-17-XX-30-XX-02-0
Press-fit in .057 mounting hole

1047



1047-3-17-XX-30-XX-02-0
Press-fit in .056 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 17 - XX - 30 - XX - 02 - 0

BASIC PART # _____
SPECIFY SHELL FINISH: _____
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#30 CONTACT (DATA ON PAGE 208)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0446-2-17-01-30-14-02-0](#) [0445-3-17-15-30-14-02-0](#) [1047-3-17-15-30-14-02-0](#) [0444-2-17-15-30-14-02-0](#) [0444-1-17-15-30-14-02-0](#) [0446-2-17-15-30-14-02-0](#) [2603-0-17-15-30-14-02-0](#) [0444-3-17-15-30-14-02-0](#) [2601-0-17-15-30-14-02-0](#) [2602-0-17-15-30-14-02-0](#)