

0355	0354	3490	3808
0355-0-15-XX-02-XX-10-0 Solder mount in .102 min. mounting hole	0354-0-15-XX-02-XX-10-0 Pentagonal press-fit in .104 min. plated thru hole	3490-0-15-XX-02-XX-10-0 Press-fit in .091 mounting hole	3808-0-15-XX-02-XX-10-0 Press-fit in .090 mounting hole

9184	9222		
9184-0-15-XX-02-XX-10-0 Bottom entry, surface mount .092 min. plated thru hole. Also available on carrier tape, Order as: 9184-0-57-XX-02-XX-10-0	9222-2-15-XX-02-XX-10-0 Bottom entry, surface mount .082 min. plated thru hole Also available on carrier tape, Order as: 9222-2-57-XX-02-XX-10-0	Carrier tape format for 9184 & 9222. 1,500 pieces per 13" reel	

--	--	--	--

SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 15 - XX - 02 - XX - 10 - 0 BASIC PART # → SPECIFY SHELL FINISH: → 01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: → 01 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL ↑ CONTACT #02 CONTACT (DATA ON PAGE 213)
--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3490-0-15-15-02-14-10-0](#)