

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002068103

Status:

Active

Overview:

Description:

1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1778, Male, with Tin (Sn) Plated Brass Contact, Bag

General	
Product Family	Crimp Terminals
Series	1778
Application	Power, Wire-to-Wire
Comments	PC Tail Brass for Standard .062" Housing
Crimp Quality Equipment	Yes
Overview	standard_062
Product Name	Standard .062"
UPC	800753693128
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.156/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Through Hole
Wire Insulation Diameter	3.00mm max.
Wire Size AWG	N/A
Wire Size mm²	N/A
Material Info	
Engineering Number	1778-(P909)L
Reference - Drawing Numbers	
Packaging Specification	PK-1190-003-001
Sales Drawing	SD-1778-X-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

1778 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-8103](#)