

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009931300](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 3.96mm Crimp Terminal Housing, Friction Ramp, 13 Circuits, Glow-Wire Capable

Documents:

3D Model	Product Specification PS-99020-0087-001 (PDF)
Drawing (PDF)	Packaging Specification PK-3069-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	3069
Application	Power, Wire-to-Board
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. KK Interconnect Solutions
Overview	KK 396
Product Name	883906174286
UPC	

Physical

Circuits (maximum)	13
Circuits Detail	13
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.282/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Material Info

Engineering Number	3069-G13
--------------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-3069-001-001
Product Specification	PS-99020-0087-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3069 Series](#)

Mates With

[2220](#) , [3190](#) , [3192](#) , [3243](#) , [3246](#) , [41661](#)
, [41662](#) , [41671](#) , [41672](#) , [41681](#) , [41682](#)
, [41701](#) , [41711](#) , [41721](#) , [41741](#) , [41761](#) ,
[41771](#) , [41772](#) , [41791](#) , [41792](#) , [42441](#) ,
[42461](#) , [42471](#) , [42491](#)

Use With

[2478 Crimp Terminals for 18-24 AWG](#), [2578 Crimp Terminals for 22-26 AWG](#)

This document was generated on 01/24/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-93-1300](#)