

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010011084

Status:

Active

Overview:

KK 508 Connector System

Description:

5.08mm Pitch KK Crimp Terminal Housing, 8 Circuits, Natural

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-99020-0087-001 (PDF)

Packaging Specification 30010001-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	<u>3001</u>
Application	Power, Wire-to-Board
Overview	<u>KK 508 Connector System</u>
Product Name	KK 508
UPC	800753612723
Physical	
Circuits (maximum)	8
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	2.228/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Engineering Number	3001-08
Reference - Drawing Numbers	
Packaging Specification	30010001-PK-000
Product Specification	PS-99020-0087-001
Sales Drawing	SDE-3001-N-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

3001 Series

Mates With

Headers 3061 , 3003 , 3061

Use With

Crimp Terminals 2478 , 2578 , 2878

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[10-01-1084](#)