

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0011020001

Status:

Active

Overview:

Application Tooling

Description:

Insertion Tool for Standard .062" Diameter Male and Female Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

Insertion

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Insertion Hand Tool

800753619920

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

HT1807

Reference - Drawing Numbers

Application Tooling Documents

TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	2061101
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel	2061131
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass	2062101

	Contact, 18-24 AWG, Reel 1.57mm Diameter, 2062103 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2062131 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel 1.57mm Diameter, 2062132 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag 1.57mm Diameter, 2065100 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, 2065101 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, 2065102 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2065103 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2065108 Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass
--	--

Contact, 18-24 AWG, Reel 1.57mm Diameter, <u>2065109</u> Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, <u>2065130</u> Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38µm Gold (Au) Plated Brass Contact, 24-30 AWG, Reel 1.57mm Diameter, <u>2065135</u> Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38µm Gold (Au) Plated Brass Contact, 24-30 AWG, Bag 1.57mm Diameter, <u>2066100</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, <u>2066101</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel Packaged 1.57mm Diameter, <u>2066102</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag Packaged 1.57mm Diameter, <u>2066103</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, <u>2066118</u> Standard .062" Pin
--

and Socket Crimp
Terminal, Series
1560, Male, with
Selective Gold
(Au) Plated Brass
Contact, Tin/Lead
Plated Crimp Area,
18-24 AWG, Reel
1.57mm Diameter, [2066119](#)
Standard .062" Pin
and Socket Crimp
Terminal, Series
1560, Male, with
Selective Gold
(Au) Plated Brass
Contact, Tin/Lead
Plated Crimp Area,
18-24 AWG, Bag
1.57mm Diameter, [2066130](#)
Standard .062" Pin
and Socket Crimp
Terminal, Series
1854, Male, with
Gold (Au) Plated
Brass Contact, 24-30
AWG, Reel
1.57mm Diameter, [2066135](#)
Standard .062" Pin
and Socket Crimp
Terminal, Series
1854, Male, with
Gold (Au) Plated
Brass Contact, 24-30
AWG, Bag
1.57mm Diameter, [39000278](#)
Standard .062" Pin
and Socket Crimp
Terminal, Series
1560, Male, with Tin
(Sn) Plated Brass
Contact, 18-24 AWG,
Reel
1.57mm Diameter, [39000280](#)
Standard .062" Pin
and Socket Crimp
Terminal, Series
1854, 3.68mm Pitch,
Male, Tin (Sn) Plated
Brass Contact, 22-28
AWG, Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-02-0001](#)