

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0011030002

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

Extraction

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Extraction Hand Tool

800753619944

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

HT2285

Reference - Drawing Numbers

Application Tooling Documents

ATS-011030002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	2061101
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel	2061131
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass	2062101

	Contact, 18-24 AWG, Reel 1.57mm Diameter, 2062103 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2062131 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Reel 1.57mm Diameter, 2062132 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag 1.57mm Diameter, 2065100 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, 2065101 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, 2065102 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2065103 Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, 2065108 Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass
--	--

Contact, 18-24 AWG, Reel 1.57mm Diameter, <u>2065109</u> Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, <u>2065130</u> Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38µm Gold (Au) Plated Brass Contact, 24-30 AWG, Reel 1.57mm Diameter, <u>2065135</u> Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with 0.38µm Gold (Au) Plated Brass Contact, 24-30 AWG, Bag 1.57mm Diameter, <u>2066100</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Reel 1.57mm Diameter, <u>2066101</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel Packaged 1.57mm Diameter, <u>2066102</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag Packaged 1.57mm Diameter, <u>2066103</u> Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Bag 1.57mm Diameter, <u>2066118</u> Standard .062" Pin
--

	and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Reel 1.57mm Diameter, 2066119 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Bag 1.57mm Diameter, 2066122 Standard .062" Pin and Socket PC Tail Terminal, Series 1778, Male, with Selective Gold (Au) Plated Brass Contact, Bag 1.57mm Diameter, 2066130 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Reel 1.57mm Diameter, 2066135 Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Bag 1.57mm Diameter, 2067103 Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged 1.57mm Diameter, 2067104 Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with .76µm Selective Gold (Au) Plated Brass Contact, Bag Packaged 1.57mm Diameter, 2068103 Standard .062" Pin and Socket PC Tail Terminal, Series 1778, Male, with Tin
--	---

(Sn) Plated Brass
Contact, Bag
Standard .062"+ 1501801016
Male Terminal,
16-18 AWG, Tin (Sn)
Plated, Reel
Standard .062"+ 1501801020
Male Terminal,
20-22 AWG, Tin (Sn)
Plated, Reel
Standard .062"+ 1501811016
Female Terminal,
16-18 AWG, Tin (Sn)
Plated, Reel
Standard .062"+ 1501811020
Female Terminal,
20-22 AWG, Tin (Sn)
Plated, Reel
1.57mm Diameter, 39000278
Standard .062" Pin
and Socket Crimp
Terminal, Series
1560, Male, with Tin
(Sn) Plated Brass
Contact, 18-24 AWG,
Reel
1.57mm Diameter, 39000280
Standard .062" Pin
and Socket Crimp
Terminal, Series
1854, 3.68mm Pitch,
Male, Tin (Sn) Plated
Brass Contact, 22-28
AWG, Reel
1.57mm Diameter, 39000338
Standard .062" Pin
and Socket Crimp
Terminal, Series
1855, 3.68mm
Pitch, Female, Tin
(Sn) Plated Brass
Contact, 22-28 AWG,
Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-03-0002](#)