

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0011404007](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Insulation Punch](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207126](#)
Comments [See Tooling Specification \(PDF\) Above](#)
Function [Cutter](#)
Geographic Area [Global](#)
Level of Automation [Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [N/A](#)
Tool Type [Applicator](#)
UPC [800754206648](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Material Info
Engineering Number [8301-1](#)
Reference - Drawing Numbers
[Application Tooling Documents](#) [ATS-STANDARD-PARTS-001](#)



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207126 Series](#)

Use With
[11402096](#) , [11402181](#) , [11402206](#) ,
[11403007](#) , [11403024](#) , [Link:11403046](#) ,
[11403096](#) , [11403099](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-40-4007](#)