

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0014600096

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version G, Positive Lock, Wire Size 28 AWG, 3.81µm Tin/Lead (SnPb), 9 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Packaging Specification PK-70873-0001-001 (PDF)


RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Ribbon Cable / Wire Trap Connectors
Series		70400
Comments		Terminals Preloaded
Component Type		Housing
Glow-Wire Capable		No
Overview		SL Modular Connectors
Product Name		SL
UPC		800753991224

Physical		
Circuits (Loaded)		9
Color - Resin		Black
Durability (mating cycles max)		25
Entry Angle		Vertical
Flammability		94V-0
Lock to Mating Part		Yes
Material - Metal		Phosphor Bronze
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		Polyester Alloy
Net Weight		1.630/g
Number of Rows		1
PCB Retention		None
Packaging Type		Tube
Pitch - Mating Interface		2.54mm
Plating min - Mating		3.810µm
Plating min - Termination		1.905µm
Polarized to Mating Part		Yes
Stackable		Yes
Surface Mount Compatible (SMC)		N/A
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		IDT or Pierce
Wire Insulation Diameter		1.35mm max.
Wire Size AWG		28
Wire/Cable Type		Discrete Wire, Ribbon Cable

Electrical		
Current - Maximum per Contact		1.2A
Voltage - Maximum		250V

Material Info		
Engineering Number		70400-0498



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70400 Series

Mates With

Single Row Housing [70018](#) , [70107](#) Version A, [70107](#) Version B, [70543](#) , [70545](#) , [70553](#) , [70555](#)

Use With

[7307](#) Tinned 28AWG, [7767](#) Topcoat 28AWG, [24241](#) Tinned 26AWG, [8996](#) Topcoat 26AWG, [24226](#) Tinned 24AWG, [8997](#) Topcoat 24AWG, [24369](#) High Flex 26AWG, [24389](#) High Flex 24AWG

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #

Reference - Drawing Numbers

Packaging Specification
Sales Drawing

PK-70873-0001-001
SDA-70400-0491-0514-001

Ribbon Cable Tool	<u>622016600</u>
Kit, Press Not	
Included	
Hawk Semi-	<u>623003100</u>
Automatic Discrete	
Wire Terminator	

This document was generated on 01/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[14-60-0096](#)