

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015247142

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit BMI Receptacle Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-In Plastic Pegs, 0.80µm Gold (Au), UL 94V-2, 14 Circuits

Documents:

- Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification 55560002-PS-CH-000 (PDF)

Product Specification 55560002-PS-ES-000 (PDF)

Product Specification 55560002-PS-SK-000 (PDF)
- Product Specification PS-5556-002-001 (PDF)

Packaging Specification PK-42385-999-001 (PDF)

Test Summary TS-5556-002-001 (PDF)

Symbol Footprint Data SYM-A42385-14XX-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

PCB Receptacles

42385

Board-to-Board, Power, Wire-to-Board

Solder Type|With Pegs

Mini-Fit Family Power Connectors

Mini-Fit BMI

800754240802

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

14

14

Natural

30

94V-2

No

Yes

None

None

Brass

Gold

Nylon

2.932/g

2

Vertical

Yes

Yes

1.00mm

Tray

4.20mm

4.20mm

Yes

Yes

No

-40° to +105°C

Through Hole

Electrical

Current - Maximum per Contact

9.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

42385 Series

Mates With

Panel Mount Plug 42475
Right Angle
Headers 42404 , 43810
Vertical
Headers 42440 , 43879 , 44068

Grounding to PCB	No
Voltage - Maximum	600V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	240
Material Info	
Engineering Number	A-42385-14A2
Reference - Drawing Numbers	
Packaging Specification	PK-42385-999-001
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-002-001
Sales Drawing	SDA-42385-X-001
Symbol/Footprint Data	SYM-A42385-14XX-001
Test Summary	TS-5556-002-001

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-24-7142