

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015474067](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Single Row, Female, Version G Receptacle, 6 Circuits

Documents:

Drawing (PDF)	Product Specification PS-70430-001 (PDF)
3D Model	Packaging Specification PK-70873-0001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19880
UL	E29179

General

Product Family	FFC/FPC Connectors
Series	70430
Overview	SL Modular Connectors
Product Name	SL
UPC	800755015720

Physical

Actuator Type	N/A
Circuits (Loaded)	6
Color - Resin	Black
Contact Position	N/A
Durability (mating cycles max)	50
Flammability	94V-0
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	0.962/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.30mm
PCB Mounting	N/A
PCB Retention	None
PCB Thickness - Recommended	1.60mm, 2.40mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to PCB	N/A
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	1.0A, 2.0A
Voltage - Maximum	250V

Material Info

Engineering Number	70430-0495
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-70873-0001-001
-------------------------	-------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[70430 Series](#)

Mates With

SL Header [70541](#) , [70543](#) , [70545](#) , [70551](#)
, [70553](#) , [70555](#) , [74099](#) , [70634](#) , [70107](#) ,
[70018](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Tool Kit for Standard [622007400](#)

Manual Press FFC

Standard Manual [622007800](#)

Press for FFC

FFC 2 thru 20 Circuit [638018550](#)

Termination Kit for

use in the Molex

TM-3000 or TM-4000

press installed

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-47-4067