

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0019092157](#)
Status: **Active**
Overview: [Standard .093" Pin and Socket Connectors](#)
Description: 2.36mm Diameter Standard .093" Pin and Socket Plug Housing with Positive Latch, UL 94V-0, with Panel Mount, 15 Circuits

Documents:
[3D Model](#) [Packaging Specification 31910002-PK-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-3191-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179


General
Product Family Crimp Housings
Series [3191](#)
Application Power, Wire-to-Wire
Comments Polarized to Mating Part
Overview [Standard .093" Pin and Socket Connectors](#)
Product Name Standard .093"
UPC 800753872592

Physical
Circuits (maximum) 15
Circuits Detail 3x5
Color - Resin Natural
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 14649.401/mg
Number of Rows 3
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 6.70mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Electrical
Current - Maximum per Contact 6.0A

Material Info
Engineering Number 3191-15P-201

Reference - Drawing Numbers
Packaging Specification 31910002-PK-000, PK-3191-001-001
Sales Drawing 31911500-SD-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[3191 Series](#)

Mates With
[19091156](#) , [19091159](#) , [5219](#)

Use With
Standard .093" Female Crimp Terminals [1189](#) , [1381](#) , [1433](#) , [4550](#) . Standard .093" Male Crimp Terminals [1190](#) , [1380](#) , [1434](#) , [1973](#) , [42138](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19-09-2157