

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022566427

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Crimp Housing, Dual Row, Version F, 42 Circuits, Black

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

Test Summary TS-70058-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

Crimp Housings

70450

Signal, Wire-to-Board

Version F, Version F

SL Modular Connectors

SL

800753779518

Physical

Breakaway

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

No

42

Black

94V-0

Receptacle

No

3.634/g

2

Bag

No

2.54mm

No

-40° to +105°C

Material Info

Engineering Number

70450-0269

Reference - Drawing Numbers

Product Specification

Sales Drawing

Test Summary

PS-70058-001, PS-70400-001

SD-70450-0250-0275

TS-70058-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

70450 Series

Mates With

2.54mm Pitch C-Grid Header 70229 , 70280 , 70246 , 70247

Use With

70058 , 71851

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-56-6427