

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0026033101

Status: Active

Overview: KK Interconnect Solutions

Description: KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, 10 Circuits, Natural

Documents:

[3D Model](#) [Product Specification PS-40-02-001 \(PDF\)](#)

[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980

General

Product Family Crimp Housings

Series 6442

Application Power, Wire-to-Board

Overview [KK Interconnect Solutions](#)

Product Name KK 396

UPC 800753587304

Physical

Circuits (maximum) 10

Color - Resin Natural

Flammability 94V-2

Gender Receptacle

Glow-Wire Capable No

Material - Resin Nylon

Net Weight 2.600/g

Number of Rows 1

Packaging Type Bag

Panel Mount No

Pitch - Mating Interface 3.96mm

Stackable No

Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 6442-10-Z

Reference - Drawing Numbers

Product Specification PS-40-02-001

Sales Drawing SD-6442-001, SD-6442-002, SD-6442-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

6442 Series

Mates With

Molex 3.96mm pitch KK headers

Use With

MarKK Crimp Terminals 45570
KK
Trifurcon Crimp Terminals 6838 , 7258

L1NK 396 Pre-Crimped Lead
797582145 , 797582146

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-03-3101](#)