

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039000128

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 22-28 AWG, Reel

- Documents:
- Drawing (PDF)

Product Specification 55560002-PS-CH-000 (PDF)

Product Specification 55560002-PS-ES-000 (PDF)

Product Specification 55560002-PS-SK-000 (PDF)

Product Specification PS-5556-001-001 (PDF)

Product Specification PS-5556-002-001 (PDF)

Application Specification 55560001-AS-000 (PDF)

Packaging Specification 55580001-PK-000 (PDF)

Test Summary 55560010-TS-000 (PDF)

Test Summary TS-5556-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	5558
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000129 (Loose)
Product Name	Mini-Fit
UPC	800753827042

Physical	
Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.119/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info	
Engineering Number	5558-PBS2

Reference - Drawing Numbers	
Application Specification	55560001-AS-000
Packaging Specification	55580001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	SD-5558-XSX-001
Test Summary	55560010-TS-000, TS-5556-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Not Contained

Status

Low-Halogen

For more information, please visit

Contact US

Search Parts in this Series

5558 Series

Use With

Mini-Fit Jr. Plug Housing 5559
Mini-Fit BMI Plug Housing 42475

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	638191000
FineAdjust Applicator for Insulation OD	639002700

1.30-1.50mm, 22-28
AWG Wire
FineAdjust Applicator639020200
for Insulation OD
1.10-1.30mm - 22-28
AWG
FineAdjust Applicator639023800
for Insulation OD
0.95-1.08mm - 22-28
AWG
T2 Terminator 639102700
for Insulation OD
1.30-1.50mm, 22-28
AWG
T2 Terminator 639120200
for insulation OD
1.10-1.30mm - 22-28
AWG
T2 Terminator 639123800
for insulation OD
0.95-1.08mm - 22-28
AWG

This document was generated on 12/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39-00-0128 \(Mouser Reel\)](#) [39-00-0128 \(Cut Strip\)](#)