

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039000280

Status:

Active

Overview:

Standard .062"+ and Standard .062" Pin and Socket Connector Systems

Description:

1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, 3.68mm Pitch, Male, Tin (Sn) Plated Brass Contact, 22-28 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-1854-002-001 (PDF)

Product Specification PS-1854-003-001 (PDF)

Packaging Specification 18540000-PK-000 (PDF)

Test Summary 15600000-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	1854
Application	Power, Wire-to-Wire
Crimp Quality Equipment Overview	Yes
	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Packaging Alternative	39000335 (Loose)
Product Name	Standard .062"
UPC	800753332799
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	143.400/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10-1.50mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A
Material Info	
Engineering Number	1854T

Reference - Drawing Numbers	
Crimp Specification	CS-1854_1855-001
Packaging Specification	18540000-PK-000
Product Specification	PS-1854-002-001, PS-1854-003-001
Sales Drawing	18540001-SD-000
Test Summary	15600000-TS-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

1854 Series

Use With

1625 Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for Standard .062" Diameter Male and Female Terminals	11020001
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002
PremiumGrade Hand Crimp Tool for Mini-	638190800

Fit Jr. Male and
Female Terminals,
22-28 AWG
Mini-Mac Applicator 638914000
for Standard .062"
Pin and Socket
Terminals, for 18-24
AWG Wire with
Insulation Diameter
1.52-3.05mm
Mini-Mac Applicator 638914100
for Standard 0.062"
Pin and Socket
Terminals, for 22-28
AWG and 24-30
AWG Wire

Japan	
Description	Product #
Applicator for M211A Bench Press, 18-28 AWG Wire	<u>11260072</u>

This document was generated on 09/13/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39-00-0280