

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0039000428**
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification PS-5556-001-001 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Product Specification PS-5556-002-001 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	Application Specification 55560001-AS-000 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	Packaging Specification 55560001-PK-000 (PDF)
Product Specification 55560008-TS-000 (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification PS-51010-007-001 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification PS-52034-005-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000429 (Loose)
Product Name	Mini-Fit
UPC	822348149391

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	130.000/mg
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Electrical


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Engineering Number	5556GS7F
--------------------	----------

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Packaging Specification	55560001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, 55560008-TS-000, PS-51010-007-001, PS-52034-005-001, PS-5556-001-001, PS-5556-002-001
Sales Drawing	SD-5556-006-001
Test Summary	55560010-TS-000, TS-5556-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

5556 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)
 Mini-Fit BMI Slide and Lock Panel
 Mount [44516](#) Mini-Fit BMI Panel Mount
 Receptacle Housing [42474](#) , [43760](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Mini-Fit Jr. Terminals FineAdjust Applicator for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	11030044 2037026300
--	--

PremiumGrade Hand638190901
Crimp Tool for Mini-
Fit Jr. Male and
Female Terminals,
18-24 AWG
FineAdjust 639015600
Applicator for 18-20
AWG and 18-24
AWG Wires with
Insulation Diameter
1.90-2.30mm
FineAdjust Applicator639023900
for Insulation OD
1.40-1.70mm - 18-24
AWG
FineAdjust Applicator639024800
for Insulation OD
2.50-2.95mm
Optimized for 18
AWG Only
FineAdjust Applicator639024900
for Insulation OD
2.30-2.60mm - 18-24
AWG
FineAdjust Applicator639047800
for Insulation OD
2.50-2.95mm, 18-24
AWG
FineAdjust Applicator639048000
for Insulation OD
1.65-2.05mm, 18-24
AWG
T2 Terminator 639115600
for insulation OD
1.90-2.30mm - 18-24
AWG
T2 Terminator 639123900
for insulation OD
1.40-1.70mm - 18-24
AWG
T2 Terminator 639124800
for insulation OD
2.50-2.95mm
optimized for 18
AWG only
T2 Terminator 639124900
for insulation OD
2.30-2.60mm - 18-24
AWG
T2 Terminator 639147800
for Mini-Fit Crimp
Terminals, 18-24
AWG with Large
Insulation ODs
T2 Terminator 639148000
for Mini-Fit Crimp
Terminals, 18-24
AWG with Smaller
Insulation ODs

This document was generated on 12/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39-00-0428 \(Cut Strip\)](#) [39-00-0428 \(Mouser Reel\)](#)