

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0082265507](#)
Status: **Active**
Description: 2.50mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 34) Stranded, Topcoat, 7 Circuits, Reel 30.48m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
Series [40160](#)
Crimp Quality Equipment Yes
Geographic Area Asia
Product Name Ribbon
UPC 800754991803

Physical

Cable Length 30.48m
Circuits (Loaded) 7
Insulation PVC
Net Weight 1120.650/g
Packaging Type Reel
Pitch - Termination Interface 2.50mm
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 26
Wire/Cable Type (7x34) Stranded, Topcoat

Electrical


Current - Maximum per Contact N/A
Voltage - Maximum 300V

Material Info

Engineering Number 40160-07-100B

Reference - Drawing Numbers

Sales Drawing SD-40160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[40160](#) Series

Use With

[42219](#) SPOX IDT Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[82-26-5507](#)