

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0150200431](#)  
**Status:** **Active**  
**Overview:** Premo-Flex Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 40 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-15020-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-15020-001-001 (PDF)</a>	



*Series image - Reference only*

**General**

Product Family	Cable
Series	<a href="#">15020</a>
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	<a href="#">Premo-Flex Cable Jumpers</a>
Product Name	Premo-Flex FFC Jumper
UPC	884982178939

**Physical**

Cable Length	102.00mm
Circuits (Loaded)	40
Material - Plating Mating	Gold
Net Weight	1.345/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-15020-001-001
Product Specification	PS-15020-001-001
Sales Drawing	SD-15020-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[15020 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[5051104091](#) , [541044031](#) , [541324062](#) ,  
[5019514010](#) , [5019514030](#) , [5019514050](#) ,  
[525594052](#) , [5034 804000](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15020-0431](#)