

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151321006

Status:

Active

Overview:

Pico-Lock Connector System

Description:

Pico-Lock-to-Pico-Lock Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 600.00mm Length, 10 Circuits, Black



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	15132
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-Lock-to-Pico-Lock
Overmolded	No
Overview	Pico-Lock Connector System
Product Name	Pico-Lock
Type	Discrete Wire Assembly
UPC	191128285261
Physical	
Cable Length	600.00mm
Circuits (Loaded)	10
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	20.000/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.50mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10mm
Wire Size AWG	24
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	2.5A
Voltage - Maximum	150V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	151321000-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

15132 Series

Mates With

Pico-Lock Header 504050

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15132-1006