

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151360506](#)
Status: **Active**
Overview: [MicroClasp Wire-to-Board System](#)
Description: MicroClasp-to-MicroClasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, 5 Circuits, White

Documents:

3D Model	Drawing (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	15136
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp-to-MicroClasp
Overmolded	No
Overview	MicroClasp Wire-to-Board System
Product Name	MicroClasp
Type	Discrete Wire Assembly
UPC	191128149532

Physical

Cable Length	600.00mm
Circuits (Loaded)	5
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	13.866/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.28mm
Wire Size AWG	22
Wire/Cable Type	UL 1061

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341708-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[15136](#) Series

Mates With

MicroClasp Vertical Header [55932](#)

MicroClasp Right Angle Header [55935](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15136-0506](#)