

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151670397

Status:

Active

Overview:

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description:

1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 305.00mm Cable Length, Tin (Sn) Plating, 22 Circuits



Series image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-15167-001-001 \(PDF\)](#)
- [Datasheet \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Cable

15167

Contacts on the same side, Type A

Yes

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Premo-Flex FFC Jumper

884982852808

Physical

Cable Length

Circuits (Loaded)

Contact Layout Type

Material - Plating Mating

Net Weight

Packaging Type

Pitch - Mating Interface

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

305.00mm

22

A (same side)

Tin

1.000/g

Bag

1.00mm

-40° to +105°C

N/A

Flat Flex Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.2A

60V AC

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-15167-001-001

SD-15167-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15167 Series

Mates With

Easy-On FFC/FPC Connector:

522072233 , 522712279 , 526102233

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15167-0397](#)