

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0152670271

Status:

Active

Overview:

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description:

1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 12 Circuits



Documents:

Drawing (PDF)

Product Specification PS-15267-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                                           |
|-------------------------------|-----------------------------------------------------------|
| General                       |                                                           |
| Product Family                | Cable                                                     |
| Series                        | 15267                                                     |
| Comments                      | Contacts on the same side, Type A                         |
| Crimp Quality Equipment       | Yes                                                       |
| Overview                      | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name                  | Premo-Flex FFC Jumper                                     |
| UPC                           | 884982441835                                              |
| Physical                      |                                                           |
| Cable Length                  | 76.00mm                                                   |
| Circuits (Loaded)             | 12                                                        |
| Contact Layout Type           | A (same side)                                             |
| Material - Plating Mating     | Tin                                                       |
| Net Weight                    | 0.699/g                                                   |
| Packaging Type                | Bag                                                       |
| Pitch - Mating Interface      | 1.00mm                                                    |
| Temperature Range - Operating | -40° to +105°C                                            |
| Wire Size AWG                 | N/A                                                       |
| Wire/Cable Type               | Flat Flex Cable                                           |
| Electrical                    |                                                           |
| Current - Maximum per Contact | 1.2A                                                      |
| Voltage - Maximum             | 60V AC                                                    |
| Material Info                 |                                                           |
| Reference - Drawing Numbers   |                                                           |
| Product Specification         | PS-15267-001-001                                          |
| Sales Drawing                 | SD-15267-001-001                                          |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15267 Series

Mates With

Easy-On FFC/FPC Connector: <br>522071233 , 522711279 , 526101233

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15267-0271