

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0152670513**
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 34 Circuits

Documents:

| | |
|--|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification PS-15267-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-15267-001-001 (PDF) | |



Series image - Reference only

General

| | |
|-------------------------|--|
| Product Family | Cable |
| Series | 15267 |
| Comments | Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes |
| Overview | Premo-Flex Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 884982447257 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 76.00mm |
| Circuits (Loaded) | 34 |
| Material - Plating Mating | Tin |
| Net Weight | 1.963/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|------------------|
| Packaging Specification | PK-15267-001-001 |
| Product Specification | PS-15267-001-001 |
| Sales Drawing | SD-15267-001 |

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

15267 Series

Mates With

Easy-On FFC/FPC Connector [522073433](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0513](#)