


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0152680173  
**Status:** Active  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 1.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Tin (Sn) Plating, 12 Circuits



**Documents:**  
[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification PS-15268-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                                    |                                                           |
|------------------------------------|-----------------------------------------------------------|
| <b>General</b>                     |                                                           |
| Product Family                     | Cable                                                     |
| Series                             | 15268                                                     |
| Comments                           | Contacts on the same side, Type A                         |
| Crimp Quality Equipment            | Yes                                                       |
| Overview                           | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name                       | Premo-Flex FFC Jumper                                     |
| UPC                                | 884982437609                                              |
| <b>Physical</b>                    |                                                           |
| Cable Length                       | 102.00mm                                                  |
| Circuits (Loaded)                  | 12                                                        |
| Contact Layout Type                | A (same side)                                             |
| Material - Plating Mating          | Tin                                                       |
| Net Weight                         | 1.087/g                                                   |
| Packaging Type                     | Bag                                                       |
| Pitch - Mating Interface           | 1.25mm                                                    |
| Temperature Range - Operating      | -40° to +105°C                                            |
| Wire Size AWG                      | N/A                                                       |
| Wire/Cable Type                    | Flat Flex Cable                                           |
| <b>Electrical</b>                  |                                                           |
| Current - Maximum per Contact      | 1.4A                                                      |
| Voltage - Maximum                  | 60V AC                                                    |
| <b>Material Info</b>               |                                                           |
| <b>Reference - Drawing Numbers</b> |                                                           |
| Product Specification              | PS-15268-001-001                                          |
| Sales Drawing                      | SD-15268-001-001                                          |

|                                                                                                                             |                   |
|-----------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br>Not Reviewed                                                                                               |                   |
| <b>EU RoHS</b><br>Not Reviewed<br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br>Not Reviewed | <b>China RoHS</b> |
| For more information, please visit <a href="#">Contact US</a>                                                               |                   |
| China ROHS                                                                                                                  | Not Reviewed      |
| ELV                                                                                                                         | Not Reviewed      |
| RoHS Phthalates                                                                                                             | Not Reviewed      |

**Search Parts in this Series**  
15268 Series

**Mates With**  
<a href="http://www.molex.com/product/ffc">Molex FFC – FPC connector</a>. Be sure to match like plating.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15268-0173](#)