

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190020040

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Avikrimp Fully Insulated Quick Disconnect, Female, for 14-16 AWG Wire, Box

Documents:

3D Model

Product Specification PS-19902-013-001 (PDF)

3D Model (PDF)

Product Specification PS-19902-014-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-19902-011-001 (PDF)

Agency Certification

UL

E79133

General

Product Family

Quick Disconnects

Series

19002

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Standard Quick-Disconnect Terminals

Product Name

Avikrimp

Type

Quick Disconnect

UPC

800753027695

Physical

Barrel Type

Closed

Color - Resin

Blue

Flammability

94V-2

Gender

Female

Glow-Wire Capable

No

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.943/g

Orientation

Straight

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.51mm

Tab Width

5.21mm

Temperature Range - Operating

-65° to +105°C

Wire Insulation Diameter

3.94mm max.

Wire Size AWG

14, 16

Wire Size mm²

1.30-2.00

Electrical

Voltage - Maximum

300V

Material Info

Engineering Number

BB-5287

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001, PS-19902-014-001

Sales Drawing

SD-19002-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19002 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640011100
Hand Crimp Tool for Avikrimp Female Fully Insulated Quick Disconnect Terminals, 14-16 AWG	
Crimp Head for the AT-200 Pneumatic Hand Tool	640051100

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19002-0040