

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190040005

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Fully Insulated Coupler, Male, for 14-16 AWG Wire, Box

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-19902-008-001 (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E79133

General

Product Family

Series

Crimp Quality Equipment

Insulated

Overview

Product Name

Type

UPC

Quick Disconnects

19004

Yes

Fully

Standard Quick-Disconnect Terminals

InsulKrimp

Quick Disconnect

800753030077

Physical

Barrel Type

Color - Resin

Flammability

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

Packaging Type

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

Blue

94V-2

Male

No

Nylon (PA)

None

Brass

Zinc Chromate

Zinc Chromate

Nylon

1.388/g

Straight

Bag

5.080µm

5.080µm

No

0.81mm

6.35mm

-65° to +105°C

4.32mm max.

14, 16

1.30-2.00

Electrical

Voltage - Maximum

600V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

BB-2262



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19004 Series

Use With

190050005 , 190050008 , 190050009

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640014700
Hand Crimp Tool for Industrial Terminals 14-22 AWG (see ATS)	
Crimp Head for the AT-200 Pneumatic Hand Tool	640054700

Reference - Drawing Numbers

Product Specification

PS-19902-008-001, PS-19902-011-001,
PS-19902-013-001

Sales Drawing

SD-19004-001-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19004-0005