

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190080002

Status:


Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Box, Tab
4.75 x 0.81mm



Series image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [3D Model \(PDF\)](#)
- [Product Specification PS-19902-005-001 \(PDF\)](#)
- [Product Specification PS-19902-011-001 \(PDF\)](#)
- [Product Specification PS-19902-013-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19008

Crimp Quality Equipment

Yes

Insulated

No

Overview

Standard Quick-Disconnect Terminals

Product Name

Krimptite

Type

Quick Disconnect

UPC

800755046519

Physical

Barrel Type

Closed

Gender

Female

Glow-Wire Capable

No

Insulation

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.614/g

Orientation

Flag

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

4.75mm

Temperature Range - Operating

Per Wire Specification

Termination Interface: Style

Crimp or Compression

Wire Size AWG

18, 20, 22

Electrical

Voltage - Maximum

Per Wire Specification

Material Info

Engineering Number

AA-1147-032

Reference - Drawing Numbers

Product Specification

PS-19902-005-001, PS-19902-011-001,
PS-19902-013-001

Sales Drawing

SD-19008-013

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19008 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand	640034200
Crimp Tool for Flag	
Krimptite/Vibrakrimp	
Un-insulated Female	
Quick Disconnect	
Terminals, 14-22	
AWG	

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19008-0002](#)