

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190230012

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm²) Wire, Box, Tab 6.35 x 0.81mm

- Documents:
- 3D Model

Product Specification PS-19902-011-001 (PDF)
- 3D Model (PDF)

Product Specification PS-19902-013-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-008-001 (PDF)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19023

Comments

Funnel Entry

Crimp Quality Equipment

Yes

Insulated

Partial

Overview

Standard Quick-Disconnect Terminals

Product Name

InsulKrimp

Type

Quick Disconnect

UPC

800753039926

Physical

Barrel Type

Closed

Color - Resin

Blue

Flammability

94V-0

Gender

Male

Glow-Wire Capable

No

Insulation

PVC

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Zinc Chromate

Material - Plating Termination

Zinc Chromate

Material - Resin

PVC

Net Weight

1.089/g

Orientation

Straight

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

-50° to +105°C

Wire Insulation Diameter

4.40mm max.

Wire Size AWG

14, 16

Wire Size mm²

1.30-2.00

Electrical

Voltage - Maximum

600V

Solder Process Data


Lead-freeProcess Capability

N/A

Material Info

Engineering Number

MCT-2X



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19023 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade	640010100
Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-008-001, PS-19902-011-001,
PS-19902-013-001
SD-19023-004-001

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19023-0012