

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190270117](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ATP Crimp Dies for VersaKrimp Ring Tongue Terminals, for Solid Copper or Steel Wire (Anti Rotation)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family
Series
Comments

Application Tooling
[207126](#)
The Crimp Tape Module [640162000](#) is a base unit that will work like an applicator in a Molex TM-3000 [638017200](#) , [638017300](#) industry standard crimp press or the Molex TM-4000 [638017600](#) industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Crimp
Global
Semi-Automatic
applicationtooling@molex.com
[Application Tooling](#)
ETC
Crimp Module
800753041189
CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

ATP-D-143

Reference - Drawing Numbers

Application Tooling Documents

ATS-190270117-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001,



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207126](#) Series

Use With

Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

Application Tooling

Description

FAQ

Product #

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	191930148
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191930151
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	191930155

TM-640160065SP-001, TM-640160065TH-001,
TM-640160065TW-001, TM-640160065VN-001

VersaKrimp Ring 191930158
Tongue Terminal
for 8 AWG Wire,
Stud Size 5/16" (M8),
Mylar Tape Carrier
D-351-38T RING 191930170
VERSAKRIMP TAPE
DBL SPACE

This document was generated on 07/31/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19027-0117](#)