

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190670055](#)
Status: **Active**
Overview:
Description: NylaKrimp Funnel Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 5/16" (M8)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19067
Crimp Quality Equipment	Yes
Overview	solderless_terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066083
Physical	
Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	6.100/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/16" (M8)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	10.87mm max.
Wire Size AWG	6
Material Info	
Engineering Number	E-957-56
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001, PS-19902-016-001
Sales Drawing	SD-19067-013-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19067](#) Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192890004
Hydraulic Dieless Crimping Tool	638161700
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	640013900
Crimp Tool Kit for 6 AWG Insulated Ring Terminals	640017770

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19067-0055](#)