

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190740010

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Steel Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier

Documents:

- 3D Model

Product Specification PS-19902-011-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Drawing (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19074

Crimp Quality Equipment

Yes

Overview

Solderless Terminals

Product Name

Krimptite

Type

Ring

UPC

800753078918

Physical

Barrel Type

Closed

Insulation

None

Material - Plating Mating

Tin

Net Weight

0.465/g

Packaging Type

Adhesive Tape on Reel

Stud Size

6 (M3.5)

Wire Size AWG

18, 20, 22

Material Info

Engineering Number

SRA-S-129-06T

Reference - Drawing Numbers

Product Specification

PS-19902-011-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Methylhexahydrophthalic
anhydride
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Aluminosilicate
Refractory Ceramic
Fibres
Boric acid
diisohexyl phthalate
Terphenyl,
hydrogenated
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
Dibutylbis(pentane-2,4-
dionato-O,O')tin
Disodium-octaborate
Dibutyltin-dichloride
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Benzo(ghi)perylene

Dipentyl phthalate
Imidazolidine-2-thione
Phenanthrene
Dihexyl-phthalate
4-aminoazobenzene
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Cyanamide, lead(2+)
salt (1:1)
Lead titanium
zirconium oxide
Dioxobis(stearato)trilead
Tetralead-trioxide-
sulphate
Pentalead-tetraoxide-
sulphate
pyrochlore, antimony
lead yellow
Cadmium
Lead
Cadmium-sulphide
Cadmium-oxide
Diboron-trioxide
1,2-Dimethoxyethane
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Pentazinc-chromate-
octahydroxide
Potassium
hydroxyoctaoxodizincatedichromate
bis(2-methoxyethyl)
ether
Boric acid, disodium
salt, hydrate
Tris(2-chloroethyl)
phosphate
Lead chromate
molybdate sulfate red
Lead chromate

**Halogen-Free
Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19074](#) Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #

ATP Crimp Dies 190270071
for the Tape Crimp
Module and ATP-101
& 301 Press

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19074-0010](#)