

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190740018](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: Krimptite Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[3D Model \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Ring and Spade Terminals
Series [19074](#)
Crimp Quality Equipment Yes
Overview [Solderless Terminals](#)
Product Name Krimptite
Type Ring
UPC 800753079021

Physical
Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Net Weight 0.554/g
Packaging Type Adhesive Tape on Reel
Stud Size 8 (M4)
Termination Interface: Style Crimp or Compression
Wire Size AWG 14, 16

Material Info
Engineering Number SRB-129-08T

Reference - Drawing Numbers
Product Specification PS-19902-011-001
Sales Drawing SD-19074-001-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[19074 Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270184

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19074-0018