

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190750003
Status: Active
Overview: Solderless Terminals
Description: InsulKrimp Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4)

Documents:
3D Model Product Specification PS-19902-011-001 (PDF)
Drawing (PDF) Product Specification PS-19902-013-001 (PDF)
3D Model (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-009-001 (PDF)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Ring and Spade Terminals
Series 19075
Crimp Quality Equipment Yes
Overview Solderless Terminals
Product Name InsulKrimp
Type Ring
UPC 800753079403

Physical
Barrel Type Closed
Flammability 94V-0
Insulation PVC
Material - Plating Mating Tin
Net Weight 0.642/g
Packaging Type Bag
Stud Size 8 (M4)
Wire Insulation Diameter 3.68mm
Wire Size AWG 18, 20, 22

Material Info
Engineering Number SRA-229-08X

Reference - Drawing Numbers
Product Specification PS-19902-009-001, PS-19902-011-001,
PS-19902-013-001
Sales Drawing 197-02



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
19075 Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640010500
Crimp Head for the AT-200 Pneumatic Hand Tool	640050500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0003](#)