

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190750011](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: InsulKrimp Steel Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)

Documents:
[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009-001 \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Ring and Spade Terminals
Series [19075](#)
Crimp Quality Equipment Yes
Overview [Solderless Terminals](#)
Product Name InsulKrimp
Type Ring
UPC 800753079564

Physical
Barrel Type Closed
Flammability 94V-0
Insulation PVC
Material - Plating Mating Tin
Net Weight 0.557/g
Packaging Type Bag
Stud Size 10 (M5)
Wire Insulation Diameter 3.68mm
Wire Size AWG 18, 20, 22

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number SRA-S-229-10X

Reference - Drawing Numbers
Product Specification PS-19902-009-001, PS-19902-011-001,
PS-19902-013-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[19075 Series](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640010500
Crimp Head for the AT-200 Pneumatic Hand Tool	640050500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0011](#)