

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190810003

Status:

Active

Description:

MULTI-STUD RING AVIKRIMP (B-5006-MS)

| | |
|----------------|--|
| Documents: | |
| 3D Model | Product Specification PS-19902-011-001 (PDF) |
| 3D Model (PDF) | Product Specification PS-19902-013-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |

| | |
|-----------------------------|------------------------------------|
| General | |
| Product Family | Ring and Spade Terminals |
| Series | 19081 |
| Crimp Quality Equipment | Yes |
| UPC | 800753084513 |
| Physical | |
| Net Weight | 1.421/g |
| Material Info | |
| Engineering Number | B-5006-MS |
| Reference - Drawing Numbers | |
| Product Specification | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing | 190810020-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19081 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

| | |
|--|-----------|
| Global | |
| Description | Product # |
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool | 640010100 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | 640050100 |
| | 640160036 |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19081-0003