

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190850008

Status:

Active

Overview:

Description:

Open Barrel Ring , Tin-Plated Steel, for 14-18 AWG Wire, Stud Size 8 (M4)

General	
Product Family	Ring and Spade Terminals
Series	19085
Crimp Quality Equipment	Yes
Overview	solderless_terminals
Product Name	N/A
Type	Ring
UPC	800755080315
Physical	
Barrel Type	Open
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.070/g
Packaging Type	Reel
Stud Size	8 (M4)
Temperature Range - Operating	149°C
Wire Insulation Diameter	N/A
Wire Size AWG	14, 16, 18
Wire Size mm²	0.80-2.00
Electrical	
Voltage - Maximum	2000V
Material Info	
Engineering Number	RZ-S-4129-08
Reference - Drawing Numbers	
Product Specification	PS-19902-006-001, PS-19902-011-001
Sales Drawing	SD-19085-002-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19085 Series

Application Tooling

FAQ

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

Mini-Mac Applicator

638815600

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19085-0008