

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190980018

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Snap Spade Terminal, for 18-22 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length

Documents:

3D Model

Product Specification PS-19902-011-001 (PDF)

Drawing (PDF)

Product Specification PS-19902-013-001 (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19098

Crimp Quality Equipment

Yes

Overview

Solderless Terminals

Product Name

Krimptite

Type

Spade Snap

UPC

800755081374

Physical

Barrel Type

Closed

Insulation

None

Material - Plating Mating

Tin

Net Weight

0.417/g

Packaging Type

Bag

Stud Size

5-6 (M3-3.5)

Wire Size AWG

18, 20, 22

Wire Size mm²

0.35-0.80

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

AA-1704-06


Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19098-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19098 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19098-0018](#)