

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190980044

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Snap Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 6 (M3.5), Length 14.86mm, Mylar Tape Carrier

Documents:

3D Model


Drawing (PDF)

3D Model (PDF)

Product Specification PS-19902-011-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19098
Crimp Quality Equipment	Yes
Overview	Solderless Terminals
Product Name	Krimptite
Type	Spade Snap
UPC	800753088269
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.609/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Size AWG	14, 16
Wire Size mm²	1.00-2.50
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	BB-1707-06T
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001
Sales Drawing	SD-19098-004-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19098 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270068
Mini-Mac Applicator, Air Feed Mylar Tape	638853900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19098-0044