

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190980049

Status:

Active

Overview:

Description:

Krimptite Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 10 (M5), 17.60mm Length

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19098
Crimp Quality Equipment	Yes
Overview	solderless_terminals
Product Name	Krimptite
Type	Spade Snap
UPC	800755081510
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.689/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size AWG	14, 16
Wire Size mm²	1.30-2.00
Material Info	
Engineering Number	BB-1717-10
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19098-004-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19098 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19098-0049