

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191300011

Status:

Active

Description:

BLOCK SPADE INSULKRIMP (B-2471-06X)

|                                                              |                                                              |
|--------------------------------------------------------------|--------------------------------------------------------------|
| <b>Documents:</b>                                            |                                                              |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Product Specification PS-19902-013-001 (PDF)</a> |
| <a href="#">Product Specification PS-19902-009-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">Product Specification PS-19902-011-001 (PDF)</a> |                                                              |
| <b>Agency Certification</b>                                  |                                                              |
| CSA                                                          | LR18689                                                      |
| UL                                                           | E32244                                                       |
| <b>General</b>                                               |                                                              |
| Product Family                                               | Ring and Spade Terminals                                     |
| Series                                                       | <a href="#">19130</a>                                        |
| Crimp Quality Equipment                                      | Yes                                                          |
| UPC                                                          | 800753101029                                                 |
| <b>Physical</b>                                              |                                                              |
| Flammability                                                 | 94V-0                                                        |
| Net Weight                                                   | 0.913/g                                                      |
| <b>Material Info</b>                                         |                                                              |
| Engineering Number                                           | B-2471-06X                                                   |
| <b>Reference - Drawing Numbers</b>                           |                                                              |
| Product Specification                                        | PS-19902-009-001, PS-19902-011-001, PS-19902-013-001         |
| Sales Drawing                                                | SD-19130-004-001                                             |

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19130](#) Series

**Application Tooling | [FAQ](#)**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

| Global                                                                                                                                                                                                         |                           |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
| Description                                                                                                                                                                                                    | Product #                 |
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool | <a href="#">640010100</a> |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool                                                                                                                   | <a href="#">640160036</a> |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19130-0011](#)